




Grinding and Polishing Consumable




Diamond Disc

Diameter: 200mm or 250mm
Granularity: W30, W15, W10



Diamond Spray Solution

Granularity: w0.5,w1,w2,w3,
w5,w7,w14,w20,w28,w40




Polishing weave

No pressure sensitive adhesive: ϕ 230-300mm,
With pressure sensitive adhesive: ϕ 200mm
Material: Plush, Panne, worsted, canvas, silk etc.



Polishing powder

Alumina: W7、W5、W3、W2、W1、W0.5
Oxidation chrome W7、W5、W3、W2、W1、W0.5



Different kind metallographic sand paper



Lubrication and cooling liquid

Mounting Press Consumable



Plastic sample clips




Cold press mould

Φ 20, Φ 25, Φ 30, Φ 40, Φ 50mm, 40X25mm



Cold press consumable



Hot press consumable

Cutter Consumable



Vertical clamps



Metallographic cutting cooling liquid



Cutting slice

Brown fused alumina and carborundum,
 White aluminium oxide and carborundum
 Carborundum
 Single crystal alumina
 Rose grain
 Φ 250×2×32mm, Φ 350×2.5×32mm, Φ 450×3.2×32mm etc.